

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.25
- 2.Voltage Rating: 125V AC DC
- 3.Current Rating: 1A AC,DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃

Part No	Pin	A	B	C
JXT-GH1.25-2PWB-P43	2	1.25	5.75	3.75
JXT-GH1.25-3PWB-P43	3	2.50	7.00	5.00
JXT-GH1.25-4PWB-P43	4	3.75	8.25	6.25
JXT-GH1.25-5PWB-P43	5	5.00	9.50	7.50
JXT-GH1.25-6PWB-P43	6	6.25	10.75	8.75
JXT-GH1.25-7PWB-P43	7	7.50	12.00	10.00
JXT-GH1.25-8PWB-P43	8	8.75	13.25	11.25
JXT-GH1.25-9PWB-P43	9	10.00	14.50	12.50
JXT-GH1.25-10PWB-P43	10	11.25	15.75	13.75
JXT-GH1.25-11PWB-P43	11	12.50	17.00	15.00
JXT-GH1.25-12PWB-P43	12	13.75	18.25	16.25
JXT-GH1.25-13PWB-P43	13	15.00	19.50	17.50
JXT-GH1.25-14PWB-P43	14	16.25	20.75	18.75
JXT-GH1.25-15PWB-P43	15	17.50	22.00	20.00
JXT-GH1.25-16PWB-P43	16	18.75	23.25	21.25

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd			
X.X ±0.30	X.° ±5°	PART NO. JXT-GH1.25-NPWB-P43		TITLE: WAFER GH1.25 贴片带扣	
.XX ±0.20	X.X° ±3°				
.XXX ±0.10	X.XX° ±1°				
UNITS	mm	DESIGN: Ethan		MANUFACTURE DWG	
MATERILA	— — —	CHED: Olvia			
FINISH	— — —	APPD: Ava			
				SCALE N:A	SHEET 1/1

