







2 Pin样式

SECTION A-A

5.75±0.25


3.40±0.20

7.00±0.25



REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	Pin	A	B
JXT-XH2.54-2PZZ-R1	2	2.5	7.5
JXT-XH2.54-3PZZ-R1	3	5.0	10.0
JXT-XH2.54-4PZZ-R1	4	7.5	12.5
JXT-XH2.54-5PZZ-R1	5	10.0	15.0
JXT-XH2.54-6PZZ-R1	6	12.5	17.5
JXT-XH2.54-7PZZ-R1	7	15.0	20.0
JXT-XH2.54-8PZZ-R1	8	17.5	22.5
JXT-XH2.54-9PZZ-R1	9	20.0	25.0
JXT-XH2.54-10PZZ-R1	10	22.5	27.5
JXT-XH2.54-11PZZ-R1	11	25.0	30.0
JXT-XH2.54-12PZZ-R1	12	27.5	32.5
JXT-XH2.54-13PZZ-R1	13	30.0	35.0
JXT-XH2.54-14PZZ-R1	14	32.5	37.5
JXT-XH2.54-15PZZ-R1	15	35.0	40.0
JXT-XH2.54-16PZZ-R1	16	37.5	42.5



适用线路板(PCB LAYOUT)

Technical Index:

1.Temperature range: -25°C~85°C.

2.Rated voltage: 250V

DC/AC(rms).

3.Rated current: 3.0A.

4.Contact resistance: ≤20mΩ.

5.Withstanding voltage: 1000V

AC/minute.

6.Insulation resistance: ≥1000MΩ.

序号	品名	材质
1	XH2.5 胶芯	PA66 UL94V-2 Red
2	XH2.5 直针 端子	Copper Alloy/ Tin Plating

TOLERANCE		 深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd	
X.X:±0.35	X.X':±3"	PART NO.	TITLE: Socket-type terminal Vertical plug
X.XX:±0.25	X.XX':±2"	JXT-XH2.54-NPZZ-R1	DESIGN: Ethan
X.XXX:±0.15			MANUFACTURE DWG
UNITS	mm	CHED: Olvia	SCALE
MATERILA	---	APPD: Ava	N:A
FINISH	---		SHEET
			1/1