







NOTES:

- 1.BASE: LCP
- 2.PIN: Brass
- 3.Solder Tab: Brass

SPECIFICATIONS:

- 1.Spacing: 1.25
- 2.Voltage Rating: 125V AC DC
- 3.Current Rating: 1A AC DC
- 4.Insulation Resistance: 100MΩ Min
- 5.Contact Resistance: 20mΩ Max
- 6.Withstanding voltage: 500V AC 1/Minute
- 7.Temperatuer Range: -25℃ ~+ 85℃



P.C.B LAYOUT

REV.	ECN NO.	DESCRIPTION	DATE	DESIGN

Part No	PIN	A	B	C
JXT-MX1.25-2PWB-P43	2	1.25	7.50	
JXT-MX1.25-3PWB-P43	3	2.50	8.75	
JXT-MX1.25-4PWB-P43	4	3.75	10.00	2.50
JXT-MX1.25-5PWB-P43	5	5.00	11.25	3.75
JXT-MX1.25-6PWB-P43	6	6.25	12.50	5.00
JXT-MX1.25-7PWB-P43	7	7.50	13.75	6.25
JXT-MX1.25-8PWB-P43	8	8.75	15.00	7.50
JXT-MX1.25-9PWB-P43	9	10.00	16.25	8.75
JXT-MX1.25-10PWB-P43	10	11.25	17.50	10.00
JXT-MX1.25-11PWB-P43	11	12.50	18.75	11.25
JXT-MX1.25-12PWB-P43	12	13.75	20.00	12.50
JXT-MX1.25-12PWB-P43	13	15.00	21.25	13.75
JXT-MX1.25-14PWB-P43	14	16.25	22.50	15.00
JXT-MX1.25-15PWB-P43	15	17.50	23.75	16.25
JXT-MX1.25-16PWB-P43	16	18.75	25.00	17.50

TOLERANCE		深圳聚兴泰电子科技有限公司 Shenzhen Juxingtai Electronic Technology Co., Ltd		
X.X ±0.30	X.* ±5°	PART NO.	TITLE:	
.XX ±0.20	X.X* ±3°	JXT-MX1.25-NPWB-P43	WAFER 1.25 卧贴	
.XXX ±0.10	X.XX* ±1°	DESIGN: Ethan	MANUFACTURE DWG	
UNITS	mm	CHED: Olvia		SCALE
MATERILA	---	APPD: Ava		SHEET
FINISH	---		N:A	1/1