


客户图

NO.	ECN NO.	DESCRIPTION	DATE
-----	---------	-------------	------



Note:

- 1: Material(材料) :
Barrel: Brass C6801 (针管: 无铅铜 C6801)
Plunger: Brass C6801 (针头: 无铅铜 C6801)
Spring: SUS304 (弹簧: SUS304)
- 2: Plating(电镀) :
Barrel: 5u' Au over 50~80u' Ni(针管: 镀金5u', 镍底50~80u'.)
Plunger: 5u' Au over 50~80u' Ni (针头: 镀金5u', 镍底50~80u'.)
Spring: No plated (弹簧: 不电镀)
- 3: Electrical(电气特性) :
Rated Current & Voltage: DC 12V;2A (额定电压&电流: 直流12V,2A)
Contact Resistance: 50 mohm Max. at working height.
接触电阻: 最大50毫欧 (在工作高度状态下)
- 4: Mechanical(机械性能) :
Force: 35g±20% at working height. (35g±20%在工作高度)。
Durability: 10.000 cycles(min) (寿命: 10000次)
- 5: WorkTemperature(工作环境):
Withstanding Higt Temperature: 280℃
Operational Temperature: -40℃~ +85℃

深圳市鑫探技术有限公司

HTTP://WWW.XYZPOGOPIN.COM
TEL:0755-28773277 FAX:0755-28891353



SCALE:	N/A	UNIT	mm	THE UNMARKED TOLERANCE ARE AS BELOW :				DESIGNED BY:	DWG. NO.	YZ221615072P-02
SHEET:	1 of 1	PROJECTION		LENGTH		ANGLE		CHECKED BY:	TITLE: Pogo pin连接器	
DATE:	2026.04.22	VER.	D.0	X.XX X.X	±0.05mm ±0.10mm ±0.20mm	X.XX X.X	±0.50° ±1.00° ±2.00°	APPROVED BY:		