







ROHS

| REV. | ECN NO. | DESCRIPTION | DRAW | DATE |
|------|---------|-------------|------|------|
|      |         |             |      |      |

- SPECIFICATIONS
- 1.Current Rating: 2A AC, DC
  - 2.Voltage Rating: 100V AC, DC
  - 3.Temperatuer Range: -40°C~+105°C
  - 4.Contact Resistance: 20mΩ Max
  - 5.Insulation Resistance: 1000MΩ Min
  - 6.Withstanding Voltang: 800V AC/minute
  - 7.Material: Wafer LCP UL94-V0  
PIN Brass Tin-plated



SECTION A



PCB LAYOUT

|                  |       |       |                                      |                          |          |    |
|------------------|-------|-------|--------------------------------------|--------------------------|----------|----|
| COSTOMER DRAWING |       |       | LAILIAN 深圳市莱联电子有限公司                  |                          |          |    |
| DRAWING          |       |       | SHENZHEN LAILIAN ELECTRONICS CO.,LTD |                          |          |    |
| CHECK            |       |       |                                      |                          |          |    |
| APPROVAL         |       |       |                                      |                          |          |    |
| TOLERANCES ARE   |       |       | TITLE                                | 针座 PIN距2.0 4PIN卧贴 (PH系列) | REV.     | A  |
| 30-150           | ±0.35 | ANGLE | PART NO.                             | LAIL-PHC2.0-4P-01-PH-WT  | UNITS    | mm |
| 10-30            | ±0.2  |       |                                      |                          |          |    |
| 5-10             | ±0.15 |       |                                      |                          |          |    |
| 0-5              | ±0.1  |       |                                      |                          |          |    |
|                  |       |       |                                      |                          | DWG. NO. |    |