





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



SPECIFICATIONS

- 1、Current Rating: 3A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -40°C TO $+105^{\circ}\text{C}$
- 4、Contact Resistance: $20\text{m}\Omega$ Max
- 5、Insulation Resistance: $1000\text{M}\Omega$ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer LCP UL94-V0
PIN Brass Tin-plated



PCB LAYOUT

Contact	Brass	Tin Plating
Solder Lug	Brass	Tin Plating
Base	LCP	UL-94V0
Part Name	Material	Plating
COSTOMER DRAWING		 深圳市莱联电子有限公司
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD
CHECK		
APPROVAL		
TOLERANCES ARE		
30-150	± 0.35	ANGLE $\pm 3^{\circ}$
10-30	± 0.2	
5-10	± 0.15	
0-5	± 0.1	
TITLE		针座 PIN距2.54 2PIN 立贴 (XH系列)
PART NO.		LAIL-PHC2.54-4P-01-XH-LT
DWG. NO.		
		Projection 