






ROHS



PCB LAYOUT

SPECIFICATIONS:

- 1.Current Rating: 3A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperatuer Range: $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$
- 4.Contact Resistance: $20\text{m}\Omega$ Max
- 5.Insulation Resistance: $1000\text{M}\Omega$ Min
- 6.WithstandingVoltang: 1000V AC/minute
- 7.Material: Wafer Nylon66 UL94-V0
PIN Brass Tin-plated



COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD										
DRAWING		TITLE					针座 PIN距2.54 4PIN弯插 (XH系列)	REV.	A				
CHECK													
APPROVAL			PART NO.		LAIL-PHC2.54-4P-01-XH-RT		UNITS		mm				
TOLERANCES ARE													
30-150		±0.35									ANGLE		
10-30		±0.2											
5-10		±0.15											
0-5		±0.1											
			±3°		DWG. NO.		Projection						