



ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

- SPECIFICATIONS
- 1.Current Rating: 2A AC, DC
 - 2.Voltage Rating: 100V AC, DC
 - 3.Temperatuer Range: -40℃~+105℃
 - 4.Contact Resistance: 20mΩ Max
 - 5.Insulation Resistance: 1000MΩ Min
 - 6.Withstanding Voltang: 800V AC/minute
 - 7.Material: Wafer LCP UL94-V0
PIN Brass Tin-plated



COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司					
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD					
CHECK								
APPROVAL								
TOLERANCES ARE			TITLE	针座 PIN距2.0 2PIN卧贴 (PH系列)	REV.	A		
30-150	±0.35	ANGLE	PART NO.	LAIL-PHC2.0-2P-01-PH-WT	UNITS	mm		
10-30	±0.2							
5-10	±0.15							
0-5	±0.1							
			DWG. NO.		Projection 			