





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 50V AC, DC
- 3、Temperatuer Range: -40℃ TO +105℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100MΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Wafer LCP UL94-V0
PIN Brass Tin-plated



PCB LAYOUT

Contact	Phosphor Bronze	Tin Plating				
Solder Lug	Phosphor Bronze	Tin Plating				
Base	LCP	UL-94V0				
Part Name	Material	Plating				
COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
DRAWING						
CHECK						
APPROVAL						
TOLERANCES ARE						
30-150	±0.35	ANGLE	TITLE	针座 PIN距1.0 4PIN 卧贴 (SH系列)	REV.	A
10-30	±0.2		PART NO.	LAIL-PHC1.0-4P-01-SH-WT	UNITS	mm
5-10	±0.15		DWG. NO.		Projection	
0-5	±0.1					