





ROHS



SPECIFICATIONS:

- 1.Current Rating: 1A AC, DC
- 2.Voltage Rating: 30V AC, DC
- 3.Temperatuer Range: $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$
- 4.Contact Resistance: $20\text{m}\Omega$ Max
- 5.Insulation Resistance: $100\text{M}\Omega$ Min
- 6.WithstandingVoltang: 200V AC/minute
- 7.Material: Wafer LCP UL94-V0
PIN Brass Tin-plated



PCB LAYOUT

Contact	Phosphor Bronze	Tin Plating
Solder Lug	Brass	Tin Plating
Base	LCP	UL-94V0
Part Name	Material	Plating
COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD
CHECK		
APPROVAL		
TOLERANCES ARE		
30-150	±0.35	ANGLE
10-30	±0.2	
5-10	±0.15	±3°
0-5	±0.1	
TITLE	针座 PIN距0.8 5PIN卧贴	REV. A
PART NO.	LAIL-PHCO. 8-5P-01-WT	UNITS mm
DWG. NO.		Projection