




ROHS


REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATIONS

1、Current Rating: 1A AC, DC
2、Voltage Rating: 125V AC, DC
3、Temperatuer Range: -40℃ To +105℃
4、Contact Resistance: 20mΩMax
5、Insulation Resistance: 100MΩMin
6、Withstanding Voltang: 500V AC/minute
7、Material: Wafer LCP UL94-V0
PIN Brass Tin-plated



SECTION A



PCB LAYOUT

Contact	Brass	Tin Plating
Solder Lug	Brass	Tin Plating
Base	LCP	UL-94V0
Part Name	Material	Plating
COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD
CHECK		
APPROVAL		
TOLERANCES ARE		
30-150	±0.35	ANGLE
10-30	±0.2	
5-10	±0.15	±3°
0-5	±0.1	
TITLE	针座 PIN距1.25 8PIN立贴 (MX1.25系列)	REV. A
PART NO.	LAIL-PHC1.25-8P-01-PB-LT	UNITS mm
DWG. NO.		Projection