






ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

- SPECIFICATIONS:
- 1.Current Rating: 2A AC, DC
 - 2.Voltage Rating: 100V AC, DC
 - 3.Temperatuer Range: -40°C~+105°C
 - 4.Contact Resistance: 20mΩ Max
 - 5.Insulation Resistance: 1000MΩ Min
 - 6.WithstandingVoltang: 800V AC/minute



SECTION A



PCB LAYOUT

Contact	Phosphor Bronze	Tin Plating
Solder Lug	Brass	Tin Plating
Base	LCP	UL-94V0
Part Name	Material	Plating
COSTOMER DRAWING		 深圳市莱联电子有限公司
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD
CHECK		
APPROVAL		
TOLERANCES ARE		TITLE 针座 PIN距2.0 2PIN立贴（PH系列）
30-150	±0.35	ANGLE
10-30	±0.2	PART NO. LAIL-PHC2. 0-2P-01-PH-LT
5-10	±0.15	UNITS mm
0-5	±0.1	DWG. NO.
		Projection 