





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

- SPECIFICATIONS:
- 1.Current Rating: 3A AC, DC
 - 2.Voltage Rating: 250V AC, DC
 - 3.Temperatuer Range: -40°C~+105°C
 - 4.Contact Resistance: 20mΩ Max
 - 5.Insulation Resistance: 1000MΩ Min
 - 6.WithstandingVoltang: 1000V AC/minute
 - 7.Material: Wafer Nylon66 UL94-V0
PIN Brass Tin-plated



COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司				
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD				
CHECK							
APPROVAL							
TOLERANCES ARE			TITLE		针座 PIN距2.54 3PIN直插 (XHB系列)	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-PHC2.5-3P-01-XHB-L	UNITS	mm	
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
			DWG. NO.	Projection			