





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATIONS

- 1、Current Rating: 1A AC, DC
- 2、Voltage Rating: 50V AC, DC
- 3、Temperatuer Range: -40℃ TO +105℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 100MΩ Min
- 6、Withstanding Voltang: 500V AC/minute
- 7、Material: Wafer LCP UL94-V0
PIN Brass Tin-plated



Contact	Phosphor Bronze	Tin Plating
Solder Lug	Phosphor Bronze	Tin Plating
Base	LCP	UL-94V0
Part Name	Material	Plating
COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD
CHECK		TITLE 针座 PIN距1.0 6PIN 卧贴 (SH系列)
APPROVAL		REV. A
TOLERANCES ARE		PART NO. LAIL-PHC1.0-6P-01-SH-WT
30-150	±0.35	UNITS mm
10-30	±0.2	DWG. NO.
5-10	±0.15	Projection
0-5	±0.1	