






ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



SECTION A



PCB LAYOUT

- SPECIFICATIONS
- 1、Current Rating: 1A AC, DC
 - 2、Voltage Rating: 125V AC, DC
 - 3、Temperatuer Range: -40℃ To +105℃
 - 4、Contact Resistance: 20mΩ Max
 - 5、Insulation Resistance: 100MΩ Min
 - 6、Withstanding Voltang: 500V AC/minute
 - 7、Material: Wafer LCP UL94-V0
PIN Brass Tin-plated

Contact	Brass	Tin Plating
Solder Lug	Brass	Tin Plating
Base	LCP	UL-94V0
Part Name	Material	Plating
COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO., LTD
DRAWING		TITLE 针座 PIN距1.25 5PIN立贴 (MX1.25系列) REV. A
CHECK		
APPROVAL		
TOLERANCES ARE		PART NO. LAIL-PHC1.25-5P-01-PB-LT UNITS mm
30-150	±0.35	DWG. NO. Projection
10-30	±0.2	
5-10	±0.15	
0-5	±0.1	
ANGLE		
±3°		