





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATIONS

- 1、Current Rating: 5A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -40℃ TO +105℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Wafer Nylon66 UL94-V0
PIN Brass Tin-plated



PCB LAYOUT

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECK					
APPROVAL					
TOLERANCES ARE		TITLE	针座 PIN距3.0 2PINx2弯插 (MX3.0系列)	REV.	A
30-150	±0.35	PART NO.	LAIL-PHC3.0-2PX2-01-MF-RT	UNITS	mm
10-30	±0.2	DWG. NO.		Projection	
5-10	±0.15				
0-5	±0.1				