





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATIONS

- 1、Current Rating: 7A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -40℃ TO +105℃
- 4、Contact Resistance: 20mΩMax
- 5、Insulation Resistance: 1000MΩMin
- 6、Withstanding Voltang: 1500V AC/minute
- 7、Material: Wafer Nylon66 UL94-V0
PIN Brass Tin-plated



PCB LAYOUT

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
CHECK						
APPROVAL						
TOLERANCES ARE			TITLE	针座 PIN距3.96 2PIN 直插 (VH系列)	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-PHC3.96-2P-01-VH-L	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1	±3°	DWG. NO.		Projection	