

ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATIONS

1、Current Rating: 1A AC, DC

2、Voltage Rating: 125V AC, DC

3、Temperatuer Range: -40℃ To +105℃





4、Contact Resistance: 20mΩ Max

5、Insulation Resistance: 100MΩ Min

6、Withstanding Voltang: 500V AC/minute

7、Material: Wafer Nylon UL94-V0

PIN Brass Tin-plated



PCB LAYOUT

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
CHECK						
APPROVAL						
TOLERANCES ARE			TITLE	针座 PIN距1.25 4PIN直插 (MX1.25系列)	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-PHC1.25-4P-01-PB-L	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
					DWG. NO.	