






ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATIONS

- 1.Current Rating: 2A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperatuer Range: -40℃~+105℃
- 4.Contact Resistance: 20mΩ Max
- 5.Insulation Resistance: 1000MΩ Min
- 6.Withstanding Voltang: 800V AC/minute
- 7.Material: Wafer Nylon66 UL94-V0
PIN Brass Tin-plated



PCB LAYOUT

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECK						
APPROVAL						
TOLERANCES ARE			TITLE	针座 PIN距2.0 5PIN直插 (PH系列)	REV.	A
30-150	±0.35	ANGLE ±3°	PART NO.	LAIL-PHC2.0-5P-01-PH-L	UNITS	mm
10-30	±0.2					
5-10	±0.15					
0-5	±0.1					
			DWG. NO.		Projection	