





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



- SPECIFICATIONS:
- 1.Current Rating: 1A AC, DC
 - 2.Voltage Rating: 30V AC, DC
 - 3.Temperatuer Range: -40°C~+105°C
 - 4.Contact Resistance: 20mΩ Max
 - 5.Insulation Resistance:100MΩ Min
 - 6.WithstandingVoltang: 200V AC/minute
 - 7.Material: Wafer LCP UL94-V0
PIN Brass Tin-plated



PCB LAYOUT

Contact	Phosphor Bronze	Tin Plating
Solder Lug	Brass	Tin Plating
Base	LCP	UL-94V0
Part Name	Material	Plating
COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO.,LTD
CHECK		
APPROVAL		
TOLERANCES ARE		TITLE 针座 PIN距0.8 8PIN卧贴
30-150	±0.35	ANGLE
10-30	±0.2	PART NO. LAIL-PHCO. 8-8P-01-WT
5-10	±0.15	UNITS mm
0-5	±0.1	DWG. NO.
		Projection