






ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATIONS:

- 1.Current Rating: 1A AC, DC
- 2.Voltage Rating: 50V AC, DC
- 3.Temperatuer Range: -40℃ To +105℃
- 4.Contact Resistance: 30mΩ Max
- 5.Insulation Resistance: 100MΩ Min
- 6.Withstanding Voltang: 500V AC/minute
- 7.Material: Wafer LCP UL94-V0
PIN Brass Tin-plated



Contact	Phosphor Bronze	Tin Plating
Solder Lug	Brass	Tin Plating
Base	LCP	UL-94V0
Part Name	Material	Plating
COSTOMER DRAWING		 深圳市莱联电子有限公司
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD
CHECK		
APPROVAL		
TOLERANCES ARE		TITLE 针座 PIN距1.25 6PIN 立贴 (GH系列)
30-150	±0.35	REV.
10-30	±0.2	ANGLE
5-10	±0.15	PART NO.
0-5	±0.1	LAIL-PHC1.25-6P-01-GH-LT
		DWG. NO.
		UNITS
		mm
		Projection
		