






ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



SECTION A



PCB LAYOUT

- SPECIFICATIONS
1. Current Rating: 1A AC, DC
 2. Voltage Rating: 125V AC, DC
 3. Temperatuer Range: -40℃ To +105℃
 4. Contact Resistance: 20mΩ Max
 5. Insulation Resistance: 100MΩ Min
 6. Withstanding Voltang: 500V AC/minute
 7. Material: Wafer LCP UL94-V0
PIN Brass Tin-plated

Contact	Brass	Tin Plating
Solder Lug	Brass	Tin Plating
Base	LCP	UL-94V0
Part Name	Material	Plating
COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD
CHECK		
APPROVAL		
TOLERANCES ARE		
30-150	±0.35	ANGLE
10-30	±0.2	
5-10	±0.15	±3°
0-5	±0.1	
TITLE	针座 PIN距1.25 4PIN立贴 (MX1.25系列)	REV. A
PART NO.	LAIL-PHC1.25-4P-01-PB-LT	UNITS mm
DWG. NO.		Projection