





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



- SPECIFICATIONS:
- 1.Current Rating: 1A AC, DC
 - 2.Voltage Rating: 30V AC, DC
 - 3.Temperatuer Range: -40°C~+105°C
 - 4.Contact Resistance: 20mΩ Max
 - 5.Insulation Resistance:100MΩ Min
 - 6.WithstandingVolang: 200V AC/minute
 - 7.Material: Wafer LCP UL94-V0
PIN Brass Tin-plated



PCB LAYOUT

Contact	Phosphor Bronze	Tin Plating			
Solder Lug	Brass	Tin Plating			
Base	LCP	UL-94V0			
Part Name	Material	Plating			
COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING					
CHECK					
APPROVAL					
TOLERANCES ARE		TITLE	针座 PIN距0.8 6PIN卧贴	REV.	A
30-150	±0.35	PART NO.	LAIL-PHCO. 8-6P-01-WT	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
ANGLE		DWG. NO.		Projection	
±3°					