





ROHS



REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATIONS:

- 1.Current Rating: 3A AC, DC
- 2.Voltage Rating: 250V AC, DC
- 3.Temperatuer Range: $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$
- 4.Contact Resistance: $20\text{m}\Omega$ Max
- 5.Insulation Resistance: $1000\text{M}\Omega$ Min
- 6.Withstanding Voltang: 1000V AC/minute
- 7.Material: Wafer LCP UL94-V0
PIN Brass Tin-plated



COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司 SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
DRAWING						
CHECK						
APPROVAL						
TOLERANCES ARE			TITLE	针座 PIN距2.54 4PIN贴片 (XH系列)	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-PHC2.54-4P-01-XH-WT	UNITS	mm
10-30	±0.2		DWG. NO.		Projection	
5-10	±0.15					
0-5	±0.1					
±3°						