





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATIONS

1、Current Rating: 1A AC, DC
2、Voltage Rating: 125V AC, DC
3、Temperatuer Range: -40℃ To +105℃
4、Contact Resistance: 20mΩ Max
5、Insulation Resistance: 100MΩ Min
6、Withstanding Voltang: 500V AC/minute
7、Material: Wafer Nylon UL94-V0
PIN Brass Tin-plated



PCB LAYOUT

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司				
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
CHECK							
APPROVAL							
TOLERANCES ARE			TITLE		针座 PIN距1.25 3PIN直插 (MX1.25系列)	REV.	A
30-150	±0.35	ANGLE ±3°	PART NO.	LAIL-PHC1.25-3P-01-PB-L	UNITS	mm	
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
			DWG. NO.		Projection		