






ROHS

| REV. | ECN NO. | DESCRIPTION | DRAW | DATE |
|------|---------|-------------|------|------|
|      |         |             |      |      |

- SPECIFICATIONS:
- 1.Current Rating: 3A AC, DC
  - 2.Voltage Rating: 250V AC, DC
  - 3.Temperatuer Range: -40°C~+105°C
  - 4.Contact Resistance: 20mΩ Max
  - 5.Insulation Resistance: 1000MΩ Min
  - 6.WithstandingVoltang: 1000V AC/minute
  - 7.Material: Wafer Nylon66 UL94-V0  
PIN Brass Tin-plated



PCB LAYOUT

|                  |       |              |                                      |                           |            |                                                                                       |
|------------------|-------|--------------|--------------------------------------|---------------------------|------------|---------------------------------------------------------------------------------------|
| COSTOMER DRAWING |       |              | LAILIAN 深圳市莱联电子有限公司                  |                           |            |                                                                                       |
| DRAWING          |       |              | SHENZHEN LAILIAN ELECTRONICS CO.,LTD |                           |            |                                                                                       |
| CHECK            |       |              |                                      |                           |            |                                                                                       |
| APPROVAL         |       |              |                                      |                           |            |                                                                                       |
| TOLERANCES ARE   |       |              | TITLE                                | 针座 PIN距2.54 3PIN弯插 (XH系列) | REV.       | A                                                                                     |
| 30-150           | ±0.35 | ANGLE<br>±3° | PART NO.                             | LAIL-PHC2.54-3P-01-XH-RT  | UNITS      | mm                                                                                    |
| 10-30            | ±0.2  |              |                                      |                           |            |                                                                                       |
| 5-10             | ±0.15 |              |                                      |                           |            |                                                                                       |
| 0-5              | ±0.1  |              |                                      |                           |            |                                                                                       |
|                  |       |              | DWG. NO.                             |                           | Projection |  |