






ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE



- SPECIFICATIONS
- 1、Current Rating: 9A AC, DC
 - 2、Voltage Rating: 300V AC, DC
 - 3、Temperatuer Range: -40℃ TO +105℃
 - 4、Contact Resistance: 20mΩ Max
 - 5、Insulation Resistance: 1000MΩ Min
 - 6、Withstanding Voltang: 1500V AC/minute
 - 7、Material: Wafer Nylon66 UL94-V0
PIN Brass Tin-plated



PCB LAYOUT

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司				
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD				
CHECK							
APPROVAL			TITLE		针座 PIN距4.2 2PINx2直插 (MX4.2系列)	REV.	A
TOLERANCES ARE							
30-150	±0.35	ANGLE	PART NO.	LAIL-PHC4.2-2PX2-01-MF-L	UNITS	mm	
10-30	±0.2						
5-10	±0.15						
0-5	±0.1	±3°	DWG. NO.			Projection	