





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

- SPECIFICATIONS:
- 1.Current Rating: 3A AC, DC
 - 2.Voltage Rating: 250V AC, DC
 - 3.Temperatuer Range: -40°C~+105°C
 - 4.Contact Resistance: 20mΩ Max
 - 5.Insulation Resistance: 1000MΩ Min
 - 6.WithstandingVoltang: 1000V AC/minute
 - 7.Material: Wafer LCP UL94-V0
PIN Brass Tin-plated



COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司					
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD					
CHECK							
APPROVAL							
TOLERANCES ARE		TITLE	针座 PIN距2.54 2PIN卧贴 (XH系列)	REV.	A		
30-150	±0.35	PART NO.	LAIL-PHC2.54-2P-01-XH-WT	UNITS	mm		
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
ANGLE		DWG. NO.		Projection 			
±3°							