





ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

- SPECIFICATIONS:
- 1.Current Rating: 3A AC, DC
 - 2.Voltage Rating: 250V AC, DC
 - 3.Temperatuer Range: -40°C~+105°C
 - 4.Contact Resistance: 20mΩ Max
 - 5.Insulation Resistance: 1000MΩ Min
 - 6.WithstandingVoltang: 1000V AC/minute
 - 7.Material: Wafer Nylon66 UL94-V0
PIN Brass Tin-plated



PCB LAYOUT

COSTOMER DRAWING			LAILIAN 深圳市莱联电子有限公司			
DRAWING			SHENZHEN LAILIAN ELECTRONICS CO.,LTD			
CHECK						
APPROVAL						
TOLERANCES ARE			TITLE	针座 PIN距2.54 2PIN直插 (XH系列)	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-PHC2.54-2P-01-XH-L	UNITS	mm
10-30	±0.2		DWG. NO.		Projection	
5-10	±0.15					
0-5	±0.1	±3°				