



ROHS





REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATIONS

- 1.Current Rating: 2A AC, DC
- 2.Voltage Rating: 100V AC, DC
- 3.Temperatuer Range: $-40^{\circ}\text{C}\sim+105^{\circ}\text{C}$
- 4.Contact Resistance: $20\text{m}\Omega$ Max
- 5.Insulation Resistance: $1000\text{M}\Omega$ Min
- 6.Withstanding Voltang: 800V AC/minute
- 7.Material: Wafer LCP UL94-V0
PIN Brass Tin-plated



SECTION A



PCB LAYOUT

COSTOMER DRAWING		LAILIAN 深圳市莱联电子有限公司			
DRAWING		SHENZHEN LAILIAN ELECTRONICS CO., LTD			
CHECK					
APPROVAL					
TOLERANCES ARE		TITLE	针座 PIN距2.0 3PIN卧贴 (PH系列)	REV.	A
30-150	±0.35	PART NO.	LAIL-PHC2.0-3P-01-PH-WT	UNITS	mm
10-30	±0.2				
5-10	±0.15				
0-5	±0.1				
		ANGLE		DWG. NO.	
		±3°			
				Projection 	