

ROHS

REV.	ECN NO.	DESCRIPTION	DRAW	DATE

SPECIFICATIONS

1、Current Rating: 9A AC, DC

2、Voltage Rating: 300V AC, DC





3、Temperatuer Range: -40℃ TO +105℃

4、Contact Resistance: 20mΩ Max

5、Insulation Resistance: 1000MΩ Min

6、Withstanding Voltang: 1500V AC/minute

7、Material: Wafer Nylon66 UL94-V0
PIN Brass Tin-plated



PCB LAYOUT

COSTOMER DRAWING			LALIAN 深圳市莱联电子有限公司				
DRAWING			SHENZHENG LAILIAN ELECTRONICS CO.,LTD				
CHECK							
APPROVAL							
TOLERANCES ARE			TITLE		针座 PIN距4.2 2PIN直插 (MX4.2系列)	REV.	A
30-150	±0.35	ANGLE	PART NO.	LAIL-PHC4.2-2P-01-MF-L	UNITS	mm	
10-30	±0.2						
5-10	±0.15						
0-5	±0.1						
			DWG. NO.		Projection		