


- 1、Current Rating: 2A AC, DC
- 2、Voltage Rating: 250V AC, DC
- 3、Temperatuer Range: -25℃~-105℃
- 4、Contact Resistance: 20mΩ Max
- 5、Insulation Resistance: 1000MΩ Min
- 6、Withstanding Voltang: 1000V AC/minute
- 7、Material: Housing LCP UL94V-0 Natural
Cap LCP UL94V-0 Natural
Contacts Brass/Sn-plated

Circuit	Part NO.	Dimensions mm			
		A	B	C	D
2	HC-PH-2A-LCP-04	2.00	4.90	6.00	1.00
3	HC-PH-3A-LCP-04	4.00	6.90	8.00	2.00
4	HC-PH-4A-LCP-04	6.00	8.90	10.00	4.00
5	HC-PH-5A-LCP-04	8.00	10.90	12.00	6.00
6	HC-PH-6A-LCP-04	10.00	12.90	14.00	6.00
7	HC-PH-7A-LCP-04	12.00	14.90	16.00	6.00
8	HC-PH-8A-LCP-04	14.00	16.90	18.00	6.00
9	HC-PH-9A-LCP-04	16.00	18.90	20.00	6.00
10	HC-PH-10A-LCP-04	18.00	20.90	22.00	6.00
11	HC-PH-11A-LCP-04	20.00	22.90	24.00	6.00
12	HC-PH-12A-LCP-04	22.00	24.90	26.00	6.00
13	HC-PH-13A-LCP-04	24.00	26.90	28.00	6.00
14	HC-PH-14A-LCP-04	26.00	28.90	30.00	6.00
15	HC-PH-15A-LCP-04	28.00	30.90	32.00	6.00
16	HC-PH-16A-LCP-04	30.00	32.90	34.00	6.00

HC-PH- N*** - LCP - * - 04



			GENERAL TOLERANCE	制 图 DRAWING	04					 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审 核 CHECK									
			X.X ±0.30	批 准 APPROVAL	产品名称 TITLE		PH(2.0) 单排 直针		版 本 REV.	A			
1	初版发行		X.XX ±0.20	比 例 SCALE	产品料号 PART NO.		HC-PH-NA-LCP-04		单 位 UNITS	mm			
序号 No.	变更内容 MODIFY CONTENT		日期 MODIFY DATE	Angle ±3.0°	投 影 Projection			材 料 MATERIAL		页 次 SHEET	1/1		


深圳市华灿天禄电子有限公司
 ShenzhenhuacantianluELECTRONICS CO.,LTD

产品名称 TITLE	PH(2.0) 单排 直针	版本 REV.	A
产品料号 PART NO.	HC-PH-NA-LCP-04	单位 UNITS	mm
材料 MATERIAL		页次 SHEET	1/1