




产品名称
Product name
▶ 2.54PH H2.5 1*Pin 180
▶ 度单排插件 PC3.0 PA6.0
PB2.5 L11.5

产品应用场景
Product application scenario
▶ 电子通讯/数码产品/家用电器
▶ 外围设备/汽车/医疗设备等.
▶ Electronic communication/
digital products/household
appliance peripherals/
▶ Automobile/medical equipment,
etc

排针系列

致力于连接器国产化
树立智能产业新标杆

产品参数/Product parameters

额定电流(Rated current): 3A AC/DC
盐雾实验 (Life Test) : 24 hours
接触电阻 (Contact Resistance) :20mΩ
绝缘电阻 (Insulation Resistance) :1000MΩ min.
耐电压 (Withstand voltage) : AC 1000V
工作温度 (Operating Temperature) : -40° C to 105°
防火等级 (Fire rating) : Polyester (UL94V-0)
触点电镀 (Dielectric Strength) :Gold Flash
耐高温范围/时长 (High temperature resistance range/duration) :260° C for5seconds
包装方式 (Packaging method) :袋装)

材质/MATERIALS:

No.	名称/NAME	材料/MATERIAL	表面处理/颜色 Surfacetreatment/color
①	端子/Terminal	Brass/C2680	镀金 gold-plating
②	塑胶/plastic cement	PBT/PA6T	黑色 Black

产品PIN位示意图/Schematic diagram of product PIN

No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B	No. of	DIM. A	DIM. B
1*1P	0.00	2.54	1*11P	25.40	27.94	1*21P	50.80	53.34	1*31P	76.20	78.74
1*2P	2.54	5.08	1*12P	27.94	30.48	1*22P	53.34	55.88	1*32P	78.74	81.28
1*3P	5.08	7.62	1*13P	30.48	33.02	1*23P	55.88	58.42	1*33P	81.28	83.82
1*4P	7.62	10.16	1*14P	33.02	35.56	1*24P	58.42	60.96	1*34P	83.82	86.36
1*5P	10.16	12.70	1*15P	35.56	38.10	1*25P	60.96	63.50	1*35P	86.36	88.90
1*6P	12.70	15.24	1*16P	38.10	40.64	1*26P	63.50	66.04	1*36P	88.90	91.44
1*7P	15.24	17.78	1*17P	40.64	43.18	1*27P	66.04	68.58	1*37P	91.44	93.98
1*8P	17.78	20.32	1*18P	43.18	45.72	1*28P	68.58	71.12	1*38P	93.98	96.52
1*9P	20.32	22.86	1*19P	45.72	48.26	1*29P	71.12	73.66	1*39P	96.52	99.06
1*10P	22.86	25.40	1*20P	48.26	50.80	1*30P	73.66	76.20	1*40P	99.06	101.60




产品编号/Product No




- 1:产品类别/Product Category
PH:排针
FH:排母
- 2:产品流水号/Product Serial Number
13:180度单排插件
- 3:产品间距/product spacing
127-1.27mm
200-2.00mm
254-2.54mm
- 4:产品PIN位/Product PIN position
11P-1*1P

- 5:上针长度/upper needle length
C60:6.0mm
- 6:下针长度/needle penetration depth
D30:3.0mm
- 7:塑胶高度/plastic height
G1-1.0 G2-1.5
G3-2.0 G4-2.54
- 8:包装方式/packaging method
P-袋装/PE B-盒装/BOX
T-管装/Tubing W-卷带/winding
- 9:电镀规格/plating specifications
T0:GF T1:1U
T3:3U T5:5U



Schematic diagram of product ordering part numbers:LCK-PH13-25411PC60D30-G4PT0





RECOMMEND P. C. B LAYOUT
PCB TOLERANCE: ± 0.05 (TOP VIEW)



产品



3#胶袋: 16*18cm



纸箱