



P.C.B LAYOUT
(TOLERANCE±0.05)

NOTE:

一.材质及电镀方式 (MATERIAL AND FINISH)

1. 塑胶 (HOUSING):LCP,
UL 94V-0 , COLOR:BLACK
2. 端子 (CONTACT):COPPER ALLOY T=0.15mm
GOLD FLASH PLATING ON CONTACT AREA,
GOLD FLASH PLATING ON SOLDER TAILS
40u" NICKEL UNDER PLATING OVER ALL
3. 固定片 (STATOR):COPPER ALLOY T=0.15mm
40u" NICKEL UNDER PLATING OVER ALL
TIN PLATED ON STATOR

二. 电气特性

1. 额定电流 (Current rating):2 A AC/DC
2. 接触电阻 (Contact resistance):100mΩ MAX
3. 绝缘电阻 (Insulation resistance):500MΩ MIN
4. 适用温度 (Operating temperature):-20℃~85℃



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X.' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: 3.1PH 6.8H 3PIN侧压电池座
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. HXCW-BB3P3166
 UNIT: mm [inch] SCALE:1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	PART NO. HXCW-BB3P3166
			DRAW NO: HVC-2512121128
			SHEET NO. 1 OF 1