





REV.	ECN NO.	REVISED	DATE

NOTE:
1.MATERIAL:
a.HOUSING:PA46 UL94 V-0 BLACK
b.CONTACT:SUS304 T=0.35MM
(SURFACE PLATING: Ni-PLATING)
SEE ORDERING INFORMATION
2.ELECTRIC:
a.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE
b.OPERATING TEMPERATURE: -10°C~+80°C

ORDERING INFORMATION
BH-18650-A6AJ037
PLATING:
A-Au-PLATING
J-Ni-PLATING
K-Sn-PLATING
MATERIAL:
6A-PA46 BLACK

电池盒
电池型号
DIP 90° TYPE

工程部
2025-06-18
LQ. HUANG



PCB Layout Diagram
Bottom View

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美用 www.meiyangdz.com			
DECIMALS: X :±0.30 X.X :±0.25 X.XX :±0.20 X.XXX :±0.10	ANGLES: X :±1° X.X :±0.5°	DSND	Huanglieqing	DATE	2025-06-18
WEIGHT:		CHKD	ZhouRuicai	DATE	2025-06-18
SHEET 1 OF 1		APVD	XueShun Yong	DATE	2025-06-18
SCALE: 1:1		SIZE: A4	VIEW:	TITLE: 电池盒BH-18650-2J Ni DIP PA46带柱	
UNIT: mm		REV.: A/0	OBJECT: MY	PART NO.: BH-18650-A6AJ037	
				DRAW NO.:MY-CP-0476	

2	TERMINAL	4	SUS304 T=0.35MM	Ni-Plating
1	HOUSING	1	PA46 UL94 V-0	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR