







| 7    |         | 8       |      |
|------|---------|---------|------|
| REV. | ECN NO. | REVISED | DATE |
|      |         |         |      |



PCB Layout Diagram  
TOP View



工程部  
2024-01-27  
H. WANG

| UNLESS OTHERWISE SPECIFIED TOLERANCES |            | MYOUNG 美用 www.meiyangdz.com |             |                           |            |
|---------------------------------------|------------|-----------------------------|-------------|---------------------------|------------|
| DECIMALS:                             | ANGLES:    | DSND                        | WangHeng    | DATE                      | 2024-01-27 |
| X :±0.30                              | X :±1°     | CHKD                        | ZhouRuicai  | DATE                      | 2024-01-27 |
| X.X :±0.25                            | X.X :±0.5° | APVD                        | XueShunyong | DATE                      | 2024-01-27 |
| X.XX :±0.20                           |            | WEIGHT:                     | SCALE:      | SIZE: A4                  | VIEW: ③ ④  |
| X.XXX :±0.10                          |            | SHEET 1 OF 1                | UNIT: mm    | REV.: A/0                 | OBJECT: MY |
|                                       |            |                             |             | TITLE: 电池扣CR1632-I Ni DIP |            |
|                                       |            |                             |             | PART NO.: MY-1632-06-J    |            |
|                                       |            |                             |             | DRAW NO.:WD-CP-0376       |            |

|     |             |      |                   |                 |
|-----|-------------|------|-------------------|-----------------|
| 1   | TERMINAL(+) | 1    | Mn Steel T=0.20mm | Ni-Plating      |
| NO. | PART NAME   | Q'TY | MATERIAL          | PLATING & COLOR |