



REV.	ECN NO.	REVISED	DATE

NOTE:

1.MATERIAL:

a.HOUSING: PA6 BLACK UL94-HB

b.CONTACT:STAINLESS STEEL

(SURFACE PLATING: Ni-PLATING)

SEE ORDERING INFORMATION





2.ELECTRIC:

a.DIELECTNIC VOLTAGE: 500V AC ONE MINUTE

b.OPERATING TEMPERATURE: -10°C~ +80°C

ORDERING INFORMATION

BH-C-A8BJ003



PCB Layout Diagram
Top View

UNLESS OTHERWISE SPECIFIED TOLERANCES		MYOUNG 美阳 www.meiyangdz.com					
DECIMALS:	ANGLES:	DSND	WangHeng	DATE	2025-09-13	TITLE:	
X :±0.30	X :±1°	CHKD	LinAnzuo	DATE	2025-09-13	电池盒BH-C-1J Ni DIP PA6	
X.X :±0.25	X.X :±0.5°	APVD	XueShun Yong	DATE	2025-09-13	PART NO.:	
X.XX :±0.20		SCALE: 1:1		SIZE: A4		BH-C-A8BJ003	
X.XXX :±0.10		UNIT: mm		REV.: A/0		DRAW NO.:WD-CP-0538	
A-PD		SHEET 1 OF 1		OBJECT: MY			

NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR
2	TERMINAL	2	STAINLESS STEEL, ø0.40MM	Ni-Plating
1	HOUSING	1	PA6 UL94-HB	BLACK