


修 订	标 记	修 改 描 要	签 名	日 期
REV	MARK	REVISION DESCRIPTION	SIGNATURE	DATE
A0		NEW DWG		2016-03-12



- 规格说明:Specifications:
- 电气特性:Electrical:
- 1. 额定电流: Current Rating
1.5A/contact terminal
 - 2. 额定电压: Voltage Rating
30V DC
 - 3. 接触阻抗:Contact Resistance
30 milliohms MAX
 - 4. 耐电压:Dielectnic Withstanding Voitage:
500 V AC AT Sea Levot
 - 5. 绝缘阻抗:Lnsulation Resistance:
1000MEGA ohms MIN

- 原材料:Matorial:
- 1. 塑胶:Housing:
Hing Temperature Tnermaplastics,
 - 2. 外壳:Shell:SPCC
Nickel Plating
 - 2. 端子>Contact:Copper Alloy C2680

- 电镀:Finish:
- 1. 端子>Contact: Plated Gold in Mating Area;
Tin On Solder Talls

		深圳市华德共创科技有限公司 Shenzhen Huade co-create Technology Co.,LTD 电话：0755-27111216 传真：0755-29940187					
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		 		TITLE: 产品名称: USB AF10.0后插后插卷边8.2黑胶			
X.X	±0.30	X.X*	±3°	APPD: 核准:	PART NO: 产品编号: USB-HXS-126DIP		
X.XX	±0.20	X.XX*	±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT
X.XXX	±0.10	X.XXX*	±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm
					CODE	NUMBER	
						A001	