


修改		标记	修改摘要	签名	日期
REV	NO	MARK	REVISION DESCRIPTION	SIGNATURE	DATE
			NEW DWG		2016-03-12



规格说明:Specifications:

电气特性:Electrical:

1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗:Contact Resistance
30 milliohms MAX
4. 耐电压:Dielectnic Withstanding Voitage:
500 V AC AT Sea Levol
5. 绝缘阻抗:Lnsulation Resistance:
1000MEGA ohms MIN

原材料:Matorial:

1. 塑胶:Housing:
Hing Temperature Tnermaplastics,
2. 外壳:Shell:SPCC
Nickel Plating
2. 端子>Contact:Copper Alloy C2680

电镀:Finish:

1. 端子>Contact: Plated Gold in Mating Area;
Tin On Solder Talls



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: 产品名称: USB AF10.0后插后插平口8.2白胶			
X.X ±0.30	X.X° ±3°	APPD: 核准:		PART NO: USB-HXS-125DIP			
X.XX ±0.20	X.XX° ±2°	CHECK: 校对: 王建业		DATE	SCALE	UNIT	CODE NUMBER
X.XXX ±0.10	X.XXX° ±1°	DRAW: 绘图: 黄艳兰		2016-03-12	1:1	mm	A001