








PCB LAYOUT



Specifications:

Poles:02

Contact resistance:≤30mΩ

Insulation resistance:≥1000MΩ

Rated voltage:400V AC DC

Rated current:0.75A AC DC

Withstand Voltage: 1800V AC/minute

Temperature Range:-25°C~ +85°C

Housing:LCP UL94V-0,Natural(Beige)

Contacts: Brass MATTE SN

Solder Tabs:Phosphor Bronze MATTE SN




深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

TEL : 0755-27111216 FAX : 0755-29940187

-TOLERANCES-
UNLESS OTHERWISE SPECIFIED
公差参数表



TITLE:
产品名称: 5.00mm电池座

X.X ±0.30 X.X° ±3°

APPD:
核准: 谢亮

PART NO:
产品编号: HDGC5003WR-S-2P-2

X.XX ±0.30 X.XX° ±2°

CHECK:
校对: 王建业

DATE SCALE UNIT CODE NUMBER

X.XXX ±0.10 X.XXX° ±1°

DRAW:
绘图: 黄艳兰

2017-12-07 1:1 mm A018