



修 订		标 记	修 改 描 要	签 名	日 期
REV		MARK	REVISION DESCRIPTION	SIGNATURE	DATE
A0			NEW DWG		2016-03-12

规格说明:Specifications:
电气特性:Electrical:
1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗:Contact Resistance
30 milliohms MAX
4. 耐电压:Dielectnic Withstanding Voitage:
500 V AC AT Sea Level
5. 绝缘阻抗:Lnsulation Resistance:
1000MEGA ohms MIN

物理性能:Mechanical:
1. 插拔力: Cnnector Mate and Unmate Force
Mate force:3.57kgf (MAX)
Unmate force:1.02kgf (MIN)
2. 端子保持力: Terminal Retenion
1.2kgf (MIN)

原材料:Material:
1. 塑胶:Housing:
Hing Temperature Ternerplastics,
U1 94V-0 LCP White/Black
2. 端子>Contact:Copper Alloy C5191
3. 外壳:Shell: Copper Alloy
电镀:Finish:
1. 端子>Contact: Piated Gold in Mating Area;
半 金 锡 1U
2. 外壳:Shell:
Nickel Plating



RECOMMENDED PCB LAYOUT
TOLERANCE:±0.05

		深圳市华德共创科技有限公司 Shenzhen Huade co-create Technology Co.,LTD 电话：0755-27111216 传真：0755-29940187						
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表			 		TITLE: 产品名称：立贴H5.0加塞编带铜壳			
X.X	±0.30	X.X*	±3°	APPD: 核准:	PART NO: 产品编号：MICRO-ZL-106PWB			
X.XX	±0.20	X.XX*	±2°	CHECK: 校对: 王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX	±0.10	X.XXX*	±1°	DRAW: 绘图: 黄艳兰	2016-03-12	1:1	mm	A001