









修订 REV NO	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
		NEW DWG		2016-03-12



**SPECIFICATIONS**  
 Current Rating: 2A AC,DC  
 Voltage Rating: 100V AC,DC  
 Temperature Range: -25°C ~ +85°C  
 Contact Resistance: 10mΩ Max.  
 Insulation Resistance: 1000MΩ Min.  
 Withstanding Voltage: 800V AC/minute  
 Pin Material: Brass/Gold-flash  
 Solder Tabs: Brass/Gold-flash  
 Material: LCP,UL94V-0  
 Color: Natural(Beige)



Circuit No.	Dimensions			
	A	B	C	D
12P	22.00	<b>30.00</b>	24.75	26.52
14P	26.00	<b>34.00</b>	28.75	30.52

		<b>深圳市华德共创科技有限公司</b> Shenzhen Huade co-create Technology Co.,LTD 电话：0755-27111216 传真：0755-29940187			
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: <b>PHA2.0卧贴</b> 产品名称:	
X.X	±0.30	X.X*	±3'	APPD: 核准:	PART NO: 产品编号: <b>C2022WR-nP</b>
X.XX	±0.20	X.XX*	±2'	CHECK: 王建业	DATE SCALE UNIT CODE NUMBER
X.XXX	±0.10	X.XXX*	±1'	DRAW: 黄艳兰 绘图:	2016-03-12 1:1 mm A001