

E		F		
修 订	标 记	修 改 描 要	签 名	日 期
REV NO	MARK	REVISION DESCRIPTION	SIGNATURE	DATE
		NEW DWG		2016-03-12

规格说明:Specifications:

电气特性:Electrical:





1. 额定电流: Current Rating
1.5A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗:Contact Resistance
30 milliohms MAX
4. 耐电压:Dielectnic Withstanding Voitage:
500 V AC AT Sea Levol
5. 绝缘阻抗:Insulation Resistance:
1000MEGA ohms MIN

原材料:Matorial:


1. 塑胶:Housing:
Hing Temperature Thermaplastics,
2. 外壳:Shell:SPCC
Nickel Plating
2. 端子>Contact:Copper Alloy C2680

电镀:Finish:

1. 端子>Contact: Plated Gold in Mating Area;
Tin On Solder Talls



Recommended P.C.B Layout



		深圳市华德共创科技有限公司 Shenzhen Huade co-create Technology Co.,LTD 电话: 0755-27111216 传真: 0755-29940187					
-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		 		TITLE: 产品名称: USB AF双层沉板平口白胶			
X.X ±0.30	X.X* ±3°	APPD: 核准:		PART NO: 产品编号: USB-HXS-113DIP			
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业		DATE	SCALE	UNIT	CODE NUMBER
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰		2016-03-12	1:1	mm	A001