







修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
AO		NEW RELEASE	黄艳兰	2021-08-22




**Specifications:**

Contact resistance: ≤10mΩ  
 Insulation resistance: ≥1000MΩ  
 Rated voltage: 125V AC DC  
 Rated current: 3.0A AC DC  
 Withstand Voltage: 500V AC/minute  
 Temperature Range: -40°C ~ +105°C  
 Housing: PA9T/LCP UL94V-0, Natural  
 Contacts: Phosphor Bronze/MATTE Sn  
 Solder Tabs: Brass/MATTE Sn



PIN	DIM A	DIM B	DIM C	PIN	DIM A	DIM B	DIM C
2	2.00	10.90	4.80	9	16.00	24.60	18.80
3	4.00	12.60	6.80	10	18.00	26.60	20.80
4	6.00	14.60	8.80	11	20.00	28.60	22.80
5	8.00	16.60	10.80	12	22.00	30.60	24.80
6	10.00	18.60	12.80	*13	24.00	32.60	26.80
7	12.00	20.60	14.80	*14	26.00	34.60	28.80
8	14.00	22.60	16.80	*15	28.00	36.60	30.80



SUGGESTED PCB LAYOUT

**深圳市华德共创科技有限公司**

Shenzhen Huade co-create Technology Co., LTD

TEL : 0755-27111216      FAX : 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表					TITLE: 产品名称:   MX-560020立贴			
X.X	±0.30	X.X°	±3°	APPD: 核准:   谢亮	PART NO: 产品编号:   HDGC2019WV-S-XP			
X.XX	±0.30	X.XX°	±2°	CHECK: 校对:   王建业	DATE	SCALE	UNIT	CODE NUMBER
X.XXX	±0.10	X.XXX°	±1°	DRAW: 绘图:   黄艳兰	2021-08-22	1:1	mm	A018