


PCB 参考安装方式

NOTES:
备注

1. Brass or purple copper, tin-plating
黄铜或紫铜，镀锡
2. Wire screw hole M5
压线螺孔M5
3. Current Rating: 60A
额定电流: 60A
4. The maximum torque of the screw hole: 2.03 N/m
螺孔最大扭矩: 2.03 N/m
5. Operating Temperature: -40°C~+125°C
工作温度: -40°C~+125°C
6. Has passed the 72 hour salt spray test
已通过72小时盐雾测试
7. There shall be no defects such as
pin deformation and burrs.
不得有脚变形，毛刺等缺陷
8. Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	制图 DRAWING	H C T L	产品名称 TITLE	版本 REV.
1	初版发行		审核 CHECK	Z F C	PCB 焊接端子 厚度1.2 插板 铜垫片 M5 4焊脚 11X10X10.5mm	A
			批准 APPROVAL	L P J	产品料号 PART NO.	单位 UNITS
			比例 SCALE		FG-RG54-12-1110-DIP-C-01	mm
			投影 Projection		材料 MATERIAL	页次 SHEET
			角度 Angle			1/1
			公差 TOL			
			5 or more			
			2~5			
			0~2			
			±0.35			
			±0.25			
			±0.15			
			±3.0°			

深圳市富港电子有限公司