


PCB 参考安装方式



- NOTES:
备注
1. Brass or purple copper, Bright tin-plating
黄铜或紫铜, 镀亮锡
 2. Wire screw hole M5
压线螺孔M5
 3. Current Rating: 70A
额定电流: 70A
 4. There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
 5. Unmarked dimensions refer to tolerances
未标注的尺寸参考公差

序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	GENERAL TOLERANCE	制图 DRAWING	H C T L	产品名称 TITLE	版本 REV.
1	初版发行		DIM 5 or more 2~5 0~2	审核 CHECK	Z F C	PCB 焊接端子 厚度1.2 插板 铜垫片 M5 4焊脚 11x9x11.5mm	A
			TOL ±0.35 ±0.25 ±0.15 ±3.0°	批准 APPROVAL	L P J	产品料号 PART NO.	单位 UNITS
			Angle	比例 SCALE		FG-RG54-12-1109-DIP-C-01	mm
				投影 Projection		材料 MATERIAL	页次 SHEET
							1/1

深圳市富港电子有限公司