



NOTES:  
备注

1. Brass or purple copper, Bright tin-plating  
黄铜或紫铜, 镀亮锡
2. Wire screw hole M5  
压线螺孔M5
3. Current Rating: 70A  
额定电流: 70A
4. There shall be no defects such as pin deformation and burrs.  
不得有脚变形, 毛刺等缺陷
5. Unmarked dimensions refer to tolerances  
未标注的尺寸参考公差

深圳市富港电子有限公司

GENERAL TOLERANCE		制图		H C T L		产品名称		版本	
DIM	TOL	审核	批准	2 F C	TITLE	厚度	抽牙	REV.	A
5 or more	±0.35	CHECK	APPROVAL	L P J	PCB 焊接端子	1.2	30x10x7.9mm		
2~5	±0.25				产品料号	M5 4焊脚			
0~2	±0.15	比例	SCALE		PART NO.				
Angle	±3.0°	投影	Projection		FG-M54-12-3010-SMT-C-01				
		变更内容	MODIFY CONTENT		材料				
		日期	MODIFY DATE		MATERIAL				
		序号	No.						
		初版发行							

