




REV.	ECN / DESCRIPTION	BY	DATE




TOP VIEW




LEFT SIDE VIEW




FRONT VIEW




RIGHT SIDE VIEW



BOTTOM VIEW




RECOMMENDED PCB LAYOUT
VIEWED FROM COMPONENT SIDE



LED Specification

Standard LED Color	LED Wavelength	Foward(A)	Foward(V)
Green	569nm	20mA	1.85-2.45V
Yellow	589nm	20mA	1.7-2.2V



TITLE:

RJ45 56带屏蔽带灯

SIZE
A4

UNITS
MM[INCH]

GENERAL TOLERANCES
UNLESS SPECIFIED

APPROVED BY:

PART NO.:

RJ-56A1188AB1A2DY1054

SACLE
1:1


REV
A0

$x \pm 0.35$
$x \pm 0.30$

	$x^{\circ} \pm 3.0^{\circ}$	CHECKED BY:
--	-----------------------------	-------------

REMARK:

SHEET
1/2






.xx±0.25
.xxx±0.10

DESIGND BY:

KYD

深圳市富港科技有限公司

A

1		2		3		4		5		6		7		8					
H		REACH & RoHS COMPLIANT								REV.		ECN / DESCRIPTION		BY		DATE		H	
G																		G	
F				RECOMMENDED PANEL CUTOUT (REFERENCE ONLY):								KEEP-OUT AREA (COMPONENT SIDE VIEW):						F	
E																		E	
D				PCB								PLUG-IN SIDE						D	
C				UNIT: MM / INCH TOLERANCES: ±0.10 / 0.004 REFERENCE ONLY								UNIT: MM / INCH TOLERANCES: ±0.10 / 0.004						C	
B																		B	
A		深圳市富港科技有限公司		TITLE: RJ45 56带屏蔽带灯		SIZE A4		UNITS MM[INCH]		GENERAL TOLERANCES UNLESS SPECIFIED		APPROVED BY:						A	
				PART NO.: RJ-56A1188AB1A2DY1054		SACLE 1:1		REV A0		.xx±0.25		.xx°±1.5°		CHECKED BY:					
				REMARK:		SHEET 2/2				.xxx±0.10		.xxx°±1.0°		DESIGND BY:					
		1		2		3		4		5		6		7		8			