






修订 REV	标记 MARK	修改摘要 REVISION DESCRIPTION	签名 SIGNATURE	日期 DATE
A0		NEW RELEASE	WANG	2019-12-26

Ordering Information:

HDGC1257WV-S-XP - *** - *** - *

- Part No.
- Material:
(Blank):Nylon 9T,UL94V-0(Ivory)
GWT:Nylon 9T,UL94V-0,GWT 750℃
- Color:
(Blank):Ivory
BK:Black BL:Blue
OR:Orange LE:Light blue
TR:Tomato red LY:Lemon yellow
MG:Moss green DPK:Dark pink
- Finish:
(Blank):Tin over Nickel
G:Gold over Nickel



SPECIFICATIONS:

Current Rating: 1A AC,DC
Voltage Rating: 50V AC,DC
Temperature Range: -25℃ ~ +85℃
Contact Resistance: 30mΩ Max.
Insulation Resistance: 100MΩ Min.
Withstanding Voltage: 100V AC/minute
Pin Material: Phosphor Bronze/Tin over Nickel
Material: Nylon 9T,UL94V-0(Ivory)

P.C.B LAYOUT

Ordering Information & Dimensions

Circuits	Dimensions(mm)		Circuits	Dimensions(mm)	
	A	B		A	B
2P	1.25	5.75	9P	10.00	14.50
3P	2.50	7.00	10P	11.25	15.75
4P	3.75	8.25	11P	12.50	17.00
5P	5.00	9.5	12P	13.75	18.25
6P	6.25	10.75	13P	15.00	19.50
7P	7.50	12.00	14P	16.25	20.75
8P	8.75	13.25	15P	17.50	22.00



深圳市华德共创科技有限公司

Shenzhen Huade co-create Technology Co.,LTD

TEL : 0755-27111216 FAX : 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表				TITLE: 产品名称: GHR1.25针座立贴			
X.X	±0.30	X.X°	±3°	APPD: 核准:	XIE	PART NO: 产品编号: HDGC1257WV-S-XP	
X.XX	±0.30	X.XX°	±2°	CHECK: 校对:	WANG	DATE	SCALE
X.XXX	±0.10	X.XXX°	±1°	DRAW: 绘图:	WANG	2019-12-26	6:1
				UNIT			
				CODE NUMBER			
				mm			
				A008			