

A

B

C

D

E

F

修 订	标 记	修 改 描 述	签 名	日 期
REV NO		NEW DRG		2016-03-12

规格说明:Specifications:

电气特性:Electrical:

1. 额定电流: Current Rating
1.0A/contact terminal
2. 额定电压: Voltage Rating
30V DC
3. 接触阻抗:Contact Resistance
50 milliohms MAX
4. 耐电压:Dielectnic Withstanding Voitage:
300 V AC AT Sea Levol
5. 绝缘阻抗:Insulation Resistance:
100MEGA ohms MIN

物理性能:Mechanical:





1. 插拔力: Cnnector Mate and Unmate Force
Mate force:3.0kgf (MAX)
Unmate force:0.7kgf (MIN)
2. 端子保持力: Terminal Retenion
0.5kgf (MIN)

原材料:Material:


1. 塑胶:Housing:
Hing Temperature Thernaplastics,
Ul 94V-0 LCP Black
2. 端子:Contact:Copper Alloy C2680
3. 外壳:Shell: Copper Alloy C2680

电镀:Finish:

1. 端子:Contact: Piated Gold in Mating Area;
Tin On Solder Talls
2. 外壳:Shell:
Nickel Plating



P. C. B LAYOUT



深圳市华德共创科技有限公司
Shenzhen Huade co-create Technology Co.,LTD
电话: 0755-27111216 传真: 0755-29940187

-TOLERANCES- UNLESS OTHERWISE SPECIFIED 公差参数表		TITLE: 产品名称: TF全塑编带	
X.X ±0.30	X.X* ±3°	APPD: 核准:	PART NO: 产品编号: K-ZD-PWB
X.XX ±0.20	X.XX* ±2°	CHECK: 校对: 王建业	DATE SCALE UNIT CODE NUMBER
X.XXX ±0.10	X.XXX* ±1°	DRAW: 绘图: 黄艳兰	2016-03-12 1:1 mm A001